Introducing

150 Series CompXeLock





CompX eLock® meets Joint Commission requirements! options:

- Door switch provides instant notification of unauthorized entry or door ajar alerts
- Using latch splitter, eLock is capable of operating two latches or doors

Network units also available.

Visit **compxelock.com** for all eLock solutions.

150 series eLock®

Keyless, non-network, electronic access control solution for cabinetry.

The CompX eLock® for cabinetry can be used in various applications; drug and supply cabinets, key control boxes, medical & personnel records.

ComiX eLock

all versions feature:

- Audit trail of last 1,500 access attempts with date, time and user name
- ◆ 250 user/supervisor codes
- Five modes of access: Keypad, Proximity card* HID, iCLASS, MiFARE and DESFire smart cards
 *Use existing identification cards
- Motor driven latching mechanism
- 6-AA battery pack; premium brand Alkaline batteries recommended (not included)
- Low battery indicator
- ◆ Jump start battery override available through mini USB communications port allows the user, with a valid credential, to access the CompX eLock® when the batteries are exhausted
- Audible alarm bolt system
- Mini USB communications port for audit trail download with optional LockView 5 software
- Compatible with 12-volt electric door strikes to control access on interior doors



Logk View SOFTWARE


LockView® 5 software features:

LockView® makes it easy to monitor audit trails for the last 1,500 access attempts, manage users and eLocks, and assign time-based restrictions and dual credential access. Downloading and uploading information is simple. Attach mini USB to communications port on eLock and standard USB to laptop.

- Provides a comprehensive audit trail of the last 1,500 access attempts; including date, time and user name
- Complies with Joint Commission standards and is 21 CFR Part 11 compliant
- When connected, LockView sends updates to the eLock. Updates can include:
 - User changes (Add / Delete / Modify Credentials)
 - eLock Changes (Add / Delete / Modify eLocks)
 - Access Rights changes
- ◆ LockView software sold separately

Minimum System Requirements

2GB RAM, 2GB free space on hard drive, 64bit Compatible, OS: Windows XP, Vista, 7. Pentium III 1.0 GHz or higher. Other configurations are acceptable; please consult factory for detailed information.



150 series cabinet eLock has three components:


Exterior mount 2.66" 2.66" 3 3 3 3 5 5.54"

Motorized gear-driven latch



Interior mount

Battery compartment







For more information, call 847.752.2500

Reorder #: F2644-035

Copyright 2017 © CompX Security Products / 847.752.2500 / compx.com / 715 Center St., Grayslake, IL 60030 Any companies and/or products referred to herein are marks or registered trademarks of their respective companies, owners and/or mark holders.